



Safety Data Sheet

According to Hazardous Products Regulation (SOR/2015-17)

Revision date: 14.04.2020

Version: 6.2

Print date: 14.04.2020

SECTION 1: Identification

Product identifier

Trade name/designation:	Acetic acid 5% v/v
Product No.:	00654
Synonymes:	none/none
CAS No.:	64-19-7
Other means of identification:	

Relevant identified uses of the substance or mixture and uses advised against

Recommended Use:	For Further Manufacturing Use Only
Uses advised against:	Not for Human or Animal Drug Use

Details of the supplier of the safety data sheet

Supplier

VWR International

Street	2360 Argentia Road
Postal code/City	Mississauga, Ontario Canada L5N 5Z7
Telephone	+1-800-932-5000 toll-free within US/Canada
Telefax:	+1-610-728-2103

Emergency phone number

Telephone +1-613-996-6666 (Canutec, 24 hrs/day, 7 days/week, Canada)

Preparation Information

VWR International - Product Information Compliance

E-mail sds@vwr.com

SECTION 2: Hazard identification

2.1 Classification of the substance or mixture

Classification according to Hazardous Products Regulation (SOR/2015-17)

This mixture is classified as not hazardous according to Hazardous Products Regulation (SOR/2015-17)





2.2 Label elements

Labelling in accordance with (SOR/2015-17)

According to Hazardous Products Regulation (SOR/2015-17) the product does not have to be labelled.

Hazards not otherwise classified (HNOC)

Not regulated

SECTION 3: Composition / information on ingredients

3.1 Substances

not applicable

3.2 Mixtures

Hazardous ingredients GHS Classification in accordance with (SOR/2015-17)

Substance name	Concentration	Identifier	Hazard classes and hazard categories
Acetic acid	5 - 10%	CAS No.: 64-19-7	Flam. Liq. 3 - H226 Skin Corr. 1A - H314

SECTION 4: First aid measures

4.1 General information

When in doubt or if symptoms are observed, get medical advice. If unconscious place in recovery position and seek medical advice. Never give anything by mouth to an unconscious person or a person with cramps. Change contaminated, saturated clothing. Do not leave affected person unattended.

In case of inhalation

Remove casualty to fresh air and keep warm and at rest. If breathing is irregular or stopped, administer artificial respiration. In case of respiratory tract irritation, consult a physician.

In case of skin contact

After contact with skin, wash immediately with plenty of water and soap. Remove contaminated, saturated clothing immediately. In case of skin reactions, consult a physician.

After eye contact

In case of contact with eyes flush immediately with plenty of flowing water for 10 to 15 minutes holding eyelids apart and consult an ophthalmologist. Protect uninjured eye. Remove contact lenses, if present and easy to do. Continue rinsing.

In case of ingestion

If accidentally swallowed rinse the mouth with plenty of water (only if the person is conscious) and obtain immediate medical attention. Do NOT induce vomiting. Give nothing to eat or drink.

4.2 Most important symptoms/effects, acute and delayed

no data available

4.3 Indication of any immediate medical attention and special treatment needed

no data available





4.4 Self-protection of the first aider

First aider: Pay attention to self-protection!

4.5 Information to physician

no data available

SECTION 5: Fire fighting measures

5.1 Extinguishing media

Suitable extinguishing media

The product itself does not burn.

Co-ordinate fire-fighting measures to the fire surroundings.

Extinguishing media which must not be used for safety reasons

no restriction

5.2 Specific hazards arising from the chemical

In case of fire may be liberated:

Carbon monoxide

Carbon dioxide (CO₂)

5.3 Advice for firefighters

DO NOT fight fire when fire reaches explosives.

Protective equipment and precautions for firefighters

Wear a self-contained breathing apparatus and chemical protective clothing.

Additional information

Do not allow run-off from fire-fighting to enter drains or water courses.

Do not inhale explosion and combustion gases.

Use water spray/stream to protect personnel and to cool endangered containers.

In case of fire: Evacuate area.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

In case of major fire and large quantities: Remove persons to safety.

6.2 Environmental precautions

Discharge into the environment must be avoided.

6.3 Methods and material for containment and cleaning up

Spilled product must never be returned to the original container for recycling. Collect in closed and suitable containers for disposal.

6.4 Additional information

Clear spills immediately.





SECTION 7: Handling and storage

7.1 Precautions for safe handling

Avoid:

Inhalation

Avoid contact with eyes and skin.

Use extractor hood (laboratory).

If handled uncovered, arrangements with local exhaust ventilation have to be used.

If local exhaust ventilation is not possible or not sufficient, the entire working area must be ventilated by technical means.

Protect from moisture.

7.2 Conditions for safe storage, including any incompatibilities

Recommended storage temperature: 15-25 °C

Keep container tightly closed and in a well-ventilated place.

7.3 Specific end use(s)

Apart from the uses mentioned in section 1.2 no other specific uses are stipulated.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Ingredient (Designation)	Regulatory information	Country	Limit value type (country of origin)	Limit value
Acetic acid	CNESST	CA	VECD	37 mg/m ³ - 15 ppm
Acetic acid	CNESST	CA	VEMP	25 mg/m ³ - 10 ppm

8.2 Engineering controls

Appropriate engineering controls

Technical measures and the application of suitable work processes have priority over personal protection equipment. If handled uncovered, arrangements with local exhaust ventilation have to be used.

Personal protection equipment (PPE)

Wear suitable protective clothing. When handling with chemical substances, protective clothing must be worn.

Eye/face protection

Eye glasses with side protection

Skin protection

Wear suitable gloves. When handling with chemical substances, protective gloves must be worn. In the case of wanting to use the gloves again, clean them before taking off and air them well. Check leak tightness/impermeability prior to use.





By short-term hand contact

Suitable material:	CR (polychloroprene, chloroprene rubber)
Thickness of the glove material:	0,13 mm
Breakthrough time (maximum wearing time):	17 min

By long-term hand contact

Suitable material:	CR (polychloroprene, chloroprene rubber)
Thickness of the glove material:	-
Breakthrough time (maximum wearing time):	> 480 min

Respiratory protection

Usually no personal respirative protection necessary.

Additional information

Wash hands before breaks and after work. Avoid contact with eyes and skin. When using do not eat, drink or smoke. Provide eye shower and label its location conspicuously.

Environmental exposure controls

no data available





SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

(a) Appearance	
Physical state:	liquid
Color:	colorless
(b) Odour:	characteristic
(c) Odour threshold:	no data available

Safety relevant basic data

(d) pH:	2.4
(e) Melting point/freezing point:	no data available
(f) Initial boiling point and boiling range:	no data available
(g) Flash point:	no data available
(h) Evaporation rate:	no data available
(i) Flammability (solid, gas):	not applicable
(j) Flammability or explosive limits	
Lower explosion limit:	no data available
Upper explosion limit:	no data available
(k) Vapour pressure:	no data available
(l) Vapour density:	no data available
(m) Relative density:	no data available
(n) Solubility(ies)	
Water solubility (g/L):	no data available
Soluble (g/L) in Ethanol:	no data available
(o) Partition coefficient: n-octanol/water:	no data available
(p) Auto-ignition temperature:	no data available
(q) Decomposition temperature:	no data available
(r) Viscosity	
Kinematic viscosity:	no data available
Dynamic viscosity:	no data available
(s) Explosive properties:	not applicable
(t) Oxidising properties:	not applicable

9.2 Other information

Bulk density:	no data available
Refraction index:	no data available
Dissociation constant:	no data available
Surface tension:	no data available
Henry's Law Constant:	no data available

SECTION 10: Stability and reactivity

10.1 Reactivity

no data available





10.2 Chemical stability

The product is chemically stable under standard ambient conditions (room temperature) .

10.3 Possibility of hazardous reactions

no data available

10.4 Conditions to avoid

no data available

10.5 Incompatible materials

no data available

10.6 Hazardous decomposition products

no data available

10.7 Additional information

no data available

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute effects

Acute oral toxicity:

Acetic acid - LD50: > 3310 mg/kg - Rat - (RTECS)

Acute dermal toxicity:

Acetic acid - LD50: > 1060 mg/kg - Rabbit - (IUCLID)

Acute inhalation toxicity:

Acetic acid - LC50: 11.4 mg/l - Rat - (National Library of Medicine ChemID Plus (NLM CIP))

Irritant and corrosive effects

Primary irritation to the skin:

not applicable

Irritation to eyes:

not applicable

Irritation to respiratory tract:

not applicable

Respiratory or skin sensitization

In case of skin contact: not sensitising

In case of inhalation: not sensitising

STOT-single exposure

not applicable

STOT-repeated exposure

not applicable





CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)

Carcinogenicity

The table below indicates whether each agency has listed any ingredient as a carcinogen.

no data available	ACGIH	IARC	NTP	OSHA

Germ cell mutagenicity

No indications of human germ cell mutagenicity exist.

Reproductive toxicity

No indications of human reproductive toxicity exist.

Aspiration hazard

not applicable

Other adverse effects

no data available

Additional information

no data available

SECTION 12: Ecological information

12.1 Ecotoxicity

Fish toxicity:

Acetic acid - LC50: 88 mg/l (96 h) - Mattson, V.R., J.W. Arthur, and C.T. Walbridge 1976. Acute Toxicity of Selected Organic Compounds to Fathead Minnows. EPA-600/3-76-097, U.S.EPA, Duluth, MN :12 p.

Daphnia toxicity:

Acetic acid - EC50: 90.1 mg/l (48 h) - Espiritu, E.Q., C.R. Janssen, and G. Persoone 1995. Cyst-Based Toxicity Tests. VII. Evaluation of the 1-h Enzymatic Inhibition Test (Fluotox) with Artemia nauplii. Environ.Toxicol.Water Qual. 10:25-34

Acetic acid - LC50: 65 mg/l (48 h) - Janssen, C.R., E.Q. Espiritu, and G. Persoone 1993. Evaluation of the new ""Enzymatic Inhibition"" Criterion for Rapid Toxicity Testing with Daphnia magna

Algae toxicity:

no data available

Bacteria toxicity:

no data available

12.2 Persistence and degradability

no data available

12.3 Bioaccumulative potential

Partition coefficient: n-octanol/water: no data available





12.4 Mobility in soil:

no data available

12.5 Results of PBT/vPvB assessment

The substances in the mixture do not meet the PBT/vPvB criteria according to REACH, annex XIII.

12.6 Other adverse effects

no data available

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Appropriate disposal / Product

Dispose according to legislation. Consult the appropriate local waste disposal expert about waste disposal.

Waste code product: no data available

Appropriate disposal / Package

Dispose according to legislation. Handle contaminated packages in the same way as the substance itself.

Additional information

no data available

SECTION 14: Transport information

Land transport (TDG)

No dangerous good in sense of this transport regulation.

Sea transport (IMDG)

No dangerous good in sense of this transport regulation.

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code not relevant

Air transport (ICAO-TI / IATA-DGR)

No dangerous good in sense of this transport regulation.

SECTION 15: Regulatory information

Safety, health and environmental regulations/legislation specific for the substance or mixture

Domestic Substance List:





SECTION 16: Other information

Abbreviations and acronyms

ACGIH - American Conference of Governmental Industrial Hygienists
DOT - Department of Transportation
IARC - International Agency for Research on Cancer
IATA-DGR - International Air Transport Association-Dangerous Goods Regulations
ICAO-TI - International Civil Aviation Organization-Technical Instructions
IMDG - International Maritime Code for Dangerous Goods
LTV - Long Term Value
NIOSH - National Institute for Occupational Safety and Health
NTP - National Toxicology Program
OSHA - Occupational Safety & Health Administration
PBT - Persistent, Bioaccumulative and Toxic
PEL - Permissible Exposure Limit
STV - Short Term Value
SVHC - Substances of Very High Concern
TDG - Transport of Dangerous Goods
TLV - Threshold Limit Value
vPvB - very Persistent, very Bioaccumulative

Additional information

Indication of changes: general update

The above information is believed to be correct but does not purport to be all-inclusive and shall be used only as a guidance. The information in this document is based on the present state knowledge and is applicable to the product with regard to appropriate safety precautions. It does not represent any guarantee of the properties of the product. VWR International and his Affiliates shall not be held liable for any damage resulting from handling.

